

## **Herz Fig No HVTMV**

WRAS Approved Herzshield thermostatic mixing valves shall be approved by the TMV scheme and meet the requirements for a type 2 & type 3 valve, complying with the NHS Model Engineering Specification DO8. Valves shall be supplied with flat-faced compression union couplings, strainers and integral, removable check valves; factory preset to 38°C but with simple adjustment and locking system for each onsite application. 15mm & 22mm valves shall be rated PN10 and have a nickel plated DZR Copper alloy body. Valves must be suitable for the following applications HP-B; HP-S; HP-W; HP-T44; HPT46; LP-BE; LP-SE; LP-WE. Valves must be installed and maintained in accordance with the relevant specification. The supplied installation and maintenance log sheet must be completed and updated as necessary.